



Application Information TS-A 7

Additives for Chemical Anchoring and Fixing Products

Additives for Chemical Anchoring and Fixing Products

In chemical anchoring, generally highly filled, two-component reaction resins are used to permanently bond anchors made of metal or reinforced plastics to mineral materials (e.g., concrete, masonry, and stone). The use of this technique permits stress-free, substance-to-substance bonding of an anchor to the material surrounding the drill hole.

The reaction resins are usually epoxides, unsaturated polyesters, vinyl esters, acrylates, and modifications of these. In practice, the reaction resins are either injected from two-component cartridges (figure 1) or inserted as capsules (figure 2) into the drill hole.

Important properties of the chemical anchors are: high mechanical resilience, excellent adhesion to the substrate, good storage stability before the chemical reaction and easy processability with low raw material costs.

This brochure summarizes our additive recommendations for this application.

Preferred additives are in bold print.

2-pack Injection Cartridge



figure 1

Chemical Resin Capsule




figure 2

Wetting and Dispersing Additives

Fillers are used to improve the mechanical properties of the system and to reduce costs. However, they increase the viscosity of the formulation and in doing so, can make processability more difficult. Suitable wetting and dispersing additives improve the wetting of the solid particles, which significantly reduces viscosity (figure 3). Alternatively, the filler content can be increased while holding the viscosity constant. Moreover, wetting and dispersing additives stabilize the fillers against sedimentation (figure 4).

Viscosity Reduction (Orthophthalic Resin with 70 % Quartz)



Brookfield RVT, #7 spindle, 5 rpm

figure 3

Stabilization Against Sedimentation



figure 4

Additive Recommendations

	Viscosity Reduction	Stabilization Against Sedimentation
Epoxy	BYK-W 985 BYK-W 980 BYK-W 996 DISPERBYK-2152	ANTI-TERRA-204 BYK-W 940
Unsaturated polyester/ vinylester (also monomer-free)	BYK-W 985 BYK-W 909 BYK-W 966 DISPERBYK-2152	BYK-W 940
Acrylate	BYK-W 969 BYK-W 9010	BYK-P 105

figure 5

Rheology Additives

The flow behavior of the resin mixture is a critical factor for composite anchors. The system must be simple to prepare and as stable as possible against sedimentation during storage. Good flow properties are required during application so that all space between the anchor and the wall of the drilled hole is filled; on the other hand, the resin should remain in the hole until it has cured and not leak out of the hole. To adjust the thixotropy of chemical fixing systems BYK offers liquid as well as solid thixotropes. The two thixotropy boosters must always be used in combination with a solid thixotrope such as GARAMITE or fumed silica.

Additive Recommendations

	Thixotropy Booster	Liquid Thixotrope	Solid Thixotrope
Epoxy	RHEOBYK-R 605 RHEOBYK-R 607*	RHEOBYK-410	GARAMITE-7305
Unsaturated polyester/ vinylester (also monomer-free)	RHEOBYK-R 605	RHEOBYK-410**	GARAMITE-1958 GARAMITE-1210
Acrylate	RHEOBYK-R 605	RHEOBYK-410**	GARAMITE-1958 GARAMITE-1210

* for the hardener ** only for cobalt-free systems

figure 6

Air Release Agents/Defoamers

Mechanical strength and chemical resistance are extremely important for composite anchors. Air entrapment in the cured system could negatively affect these properties. To achieve optimal deaeration, resin-specific additives are added that spontaneously deaerate the resin during preparation and improve application.

Deaeration of an Unsaturated Polyester




figure 7

Additive Recommendations

Epoxy	BYK-A 530 BYK-A 501
Unsaturated polyester	BYK-A 555 BYK-A 515
Vinylester	BYK-A 515
Styrene-free polyester/vinylester	BYK-A 530 BYK-A 555
Acrylate	BYK-A 515 BYK-070

figure 8

Surface-active Additives

The often dusty surface of the mineral substrate makes wetting and saturation of the substrate difficult and the consequence is that the resin and substrate are not sufficiently bonded together. The use of surface-active additives, which are generally based on modified polysiloxanes, significantly reduces the surface tension of the resin (figure 9). The penetration of the resin into the substrate occurs more readily since the cohesion to the wall of the drilled hole becomes stronger than the adhesion of the liquid particles to each another.

Reduction of Surface Tension




figure 9

Additive Recommendations

Epoxy	BYK-306 BYK-310
Unsaturated polyester/vinylester (also monomer-free)	BYK-330 BYK-306 BYK-310
Acrylate	BYK-306 BYK-378

figure 10

For more information about our additives and instruments, as well as our additive sample orders please visit:

www.byk.com

Additives:

BYK-Chemie GmbH
P.O. Box 100245
46462 Wesel
Germany
Tel +49 281 670-0
Fax +49 281 65735

info@byk.com

Instruments:

BYK-Gardner GmbH
P.O. Box 970
82534 Geretsried
Germany
Tel +49 8171 3493-0
+49 800 427-3637
Fax +49 8171 3493-140

info.byk.gardner@altana.com



ACTAL®, ADD-MAX®, ADD-VANCE®, ADJUST®, ADVITROL®, ANTI-TERRA®, AQUACER®, AQUAMAT®, AQUATIX®, BENTOLITE®, BYK®, BYK®-DYNWET®, BYK®-SILCLEAN®, BYKANOL®, BYKETOL®, BYKJET®, BYKO2BLOCK®, BYKOPLAST®, BYKUMEN®, CARBOBYK®, CERACOL®, CERAFAC®, CERAFLOUR®, CERAMAT®, CERATIX®, CLAYTONE®, CLOISITE®, DISPERBYK®, DISPERPLAST®, FULACOLOR®, FULCAT®, GARAMITE®, GELWHITE®, HORDAMER®, LACTIMON®, LAPONITE®, MINERAL COLLOID®, MINERPOL®, NANOBYK®, OPTIBENT®, OPTIFLO®, OPTIGEL®, PAPERBYK®, PERMONT®, POLYAD®, PRIEX®, PURE THIX®, RECYCLOBLEND®, RECYCLOSORB®, RECYCLOSTAB®, RHEOBYK®, RHEOCIN®, RHEOTIX®, SCONA®, SILBYK®, TIXOGEL®, VISCOBYK® and Y 25® are registered trademarks of the BYK group.

The information herein is based on our present knowledge and experience. The information merely describes the properties of our products but no guarantee of properties in the legal sense shall be implied. We recommend testing our products as to their suitability for your envisaged purpose prior to use. No warranties of any kind, either express or implied, including warranties of merchantability or fitness for a particular purpose, are made regarding any products mentioned herein and data or information set forth, or that such products, data or information may be used without infringing intellectual property rights of third parties. We reserve the right to make any changes according to technological progress or further developments.

This issue replaces all previous versions – Printed in Germany